





Space between pressure plate and supporting column should be kept free from fixed installations!

*) Recommended free space for opening and closing to be applied on both sides

Technical drawing of the front view of a rectangular plate. The overall dimensions are 320 mm in width and 890 mm in height. The plate features four large circular features labeled S1, S2, S3, and S4, arranged in a 2x2 grid. Each of these features has a central crosshair and is surrounded by smaller circular features. A central rectangular feature with a wavy line is located between S1 and S3. The distance between the centers of the top two features (S1 and S4) is 110 mm. The distance between the centers of the bottom two features (S2 and S3) is 140 mm. The distance between the center of S1 and the center of S2 is 140 mm. The distance from the bottom edge to the center of the bottom features is 140 mm. The thickness of the plate is indicated as 8 mm.



(MOVABLE)



NO. OF UNITS

1

CHANNEL ARRANGEMENT 1*22 H
/ 1*22 H



T6-PFM

Do not use this drawing for foundation bolting or piping layout

DATE 2/21/22
REVISION 0